

ISO 9000 CERTIFIED A&D Company, Limited http://www.aandd.jp

Clearly a Better Value



Fast Weighing Ref for Efficient Weig

The New FG series accomplishes fast weighing response time and excellent feature of a three weighing resolution function enables from Normal resolution of 1/3000, High resolution of 1/6000 (or any weighing demand.



sponse hing Applications!

l accurate result to suit any weighing applications. Furthermore its the user to select the weighing resolution in the Function setting 1/7500) and Higher resolution of 1/12000 (or 1/15000), to meet



Three weighing resolutions

Selectable from Normal resolution (1/3000), High resolution (1/6000 for 30kg and 60kg weighing capacity) and Higher resolution (1/12000 for 60kg and 1/15000 for 30kg and 150kg weighing capacity) by function setting

Counting function

Useful in piece counting applications with sample size of 5, 10, 20, 50 and 100 pcs for unit weight registration

Comparator function COMPARATOR

HI / OK / LO comparator indication and optional comparator relay output (FG-24) for checkweighing applications

Calibration function FPC

Easy and simple to calibrate the scale with external calibration mass for accurate weighing

Auto-power OFF function **«**OFF

Saves power consumption by automatically switching itself off when the scale displays zero for approx. five minutes

Selectable two sizes of stainless steel weighing pan

Stainless steel weighing pan is easy to clean and weighing pan of size of M size (300 x 380mm) or L size (390 x 530mm) can be selected

Two types of power supply

AC Adapter for permanent installation applications or dry batteries of 4 x C size (R14P/LR14) for applications in locations with no AC power supply

Low power supply indication function

Easy to know when power supply is low with the display of "Lb1" for AC power supply and "Lb0" for dry batteries

Filtering function

Filtering levels of Slow, Normal and Fast are selectable to suit weighing environment conditions

Leveling foot and Leveling bubble

Easy and simple to adjust the level of the scale for accurate weighing

Display column and Tilt display pod

The column and tilting angle of the display unit is adjustable for better reading of display

Status indicator function

The display has status indicators of Stable, Net and Zero for easy operation

Power-ON Zero function

Takes Zero as its center when power is ON for accurate weighing

Gravity acceleration correction function

Adjustable gravity acceleration for accurate weighing

Optional RS-232C and Comparator Output REX22C

Easy to connect peripherals such as printer, comparator light and computer for weighing system applications

FG Series Specifications

	FG-30KAM FG-30KBM	FG-60KAM FG-60KBM	FG-150KAM FG-150KBM	FG-60KAL	FG-150KAL
Weight capacity (kg)	30	60	150	60	150
Min. display (kg)	0.01	0.02	0.05	0.02	0.05
	0.005*	0.01*	0.02*	0.01*	0.02*
	0.002	0.005	0.01	0.005	0.01
Weight capacity (lb)**	60	150	300	150	300
Min. display (lb)**	0.02	0.05	0.1	0.05	0.1
	0.01*	0.02*	0.05*	0.02*	0.05*
	0.005	0.01	0.02	0.01	0.02
Weight capacity (oz)**	960	2400	4800	2400	4800
Min. display (oz)**	0.5	1	2	1	2
	0.2*	0.5*	1*	0.5*	1*
	0.1	0.2	0.5	0.2	0.5
No. of samples	5 (can be changed to 10, 20, 50 or 100) pieces				
Max. counts	120,000 pcs	96,000 pcs	120,000 pcs	96,000 pcs	120,000 pcs
Min. unit weight	0.25g	0.625g	1.25g	0.625g	1.25g
Repeatability (Std. deviation)	0.005kg	0.01kg	0.02kg	0.01kg	0.02kg
Linearity error	±0.01kg	±0.02kg	±0.05kg	±0.02kg	±0.05kg
Sensitivity drift	±20ppm /°C (10°C~30°C / 50°F~86°F)				
Display	7 segment LCD display (Character height 26mm)				
Display update	10 times per second				
Operating temp	-10°C~40°C / 14°F~104°F, less than 85% RH (no condensation)				
Power supply	AC adapter or C size (R14P / LR14) x 4 batteries				
Battery operating	Approximately 150 hours with alkaline dry cell battery				
Weighing pan size	300 x 380mm / 11.8 x 15.0inches			390 x 530mm / 15.4 x 20.9inches	
Dimension	FG-KAM: 300(W) x 624(D) x 781(H)mm / FG-KBM: 380(W) x 464(D) x 118(H)mm			390(W) x 771(D) x 781(H)mm	
Weight (approximately)	FG-KAM: 11.2kg / FG-KBM: 9.7kg			16.4kg	
Calibration weight (Factory setting)	30kg / 60lb	60kg / 150lb	150kg / 300lb	60kg / 150lb	150kg / 300lb

* Factory setting ** U.S.A. version only

Options

FG-23 RS-232C serial interface

FG-24 RS-232C serial interface and comparator relay output

Accessories

AD-8121B Dot Matrix Compact Printer AD-8118B Universal Printer





A&D Company, Limiled 3-23-14 Higashi-Ikebukuro, Toshima-ku, Tokyo 170-0013 JAPAN Telephone: [81](3) 5391-6132 Fax: [81](3) 5391-6148 http://www.aandd.jp

A&D ENGINEERING, INC. 1555 McCandless Drive, Milpitas, CA. 95035 U.S.A. Telephone:[1](408) 263-5333 Fax:[1](408) 263-0119

A&D MERCURY PTY, LTD. 32 Dew Street, Thebarton, South Australia 5031 AUSTRALIA Telephone:[61](8) 8301-8100 Fax:[61](8) 8352-7409

A&D INSTRUMENTS LTD.

Unit 24/26 Blacklands Way Abingdon Business Park, Abingdon, Oxon OX14 1DY United Kingdom Telephone:[44](1235) 550420 Fax:[44](1235) 550485

German Sales Office> Große Straße 13 b 22926 Ahrensburg GERMANY Telephone:[49](0) 4102 459230 Fax:[49](0) 4102 459231

A&D KOREA Limited Manhattan Bldg. 8F, 36-2 Yoido-dong, Youngdeungpo-gu, Seoul, KOREA Telephone:[82](2) 780-4101 Fax:[82](2) 782-4280